ATGBICS

ATGBICS XBR-000164 Brocade Compatible Transceiver 8 x SFP+ 8G Fibre Channel-SW (850nm, MMF, 150m, DOM)

Brand : ATGBICS

Product code: XBR-000164-C

Product name : XBR-000164 Brocade Compatible Transceiver 8 x SFP+ 8G Fibre Channel-SW (850nm, MMF, 150m, DOM)



XBR-000164 Brocade Compatible Transceiver 8 x SFP+ 8G Fibre Channel-SW (850nm, MMF, 150m, DOM)

ATGBICS XBR-000164 Brocade Compatible Transceiver 8 x SFP+ 8G Fibre Channel-SW (850nm, MMF, 150m, DOM):

ATGBICS XBR-000164 8GBase-SW fibre Channel supports a distance of up to 300m over multi-mode fibre (MMF) using a wavelength of 850nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of Brocade XBR-000164= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.

Performance	
SFP transceiver type *	Fiber optic
Maximum data transfer rate *	8000 Mbit/s
Interface type *	SFP+
Single-mode fiber (SMF) supported	✗
Multi-mode fiber (MMF) supported	✓
Fiber optic connector	LC
SFP transceiver standard	SW
Maximum transfer distance	150 m
Wavelength	850 nm
Ethernet LAN	✓
Ethernet interface type	8 Gigabit Ethernet
Digital Diagnostics Monitoring (DDM)	✓
Wavelength-division multiplexing (WDM)	✗

Features	
Product colour	Silver
Housing material	Metal
Plug and Play	✓
Hot-Plug support	✓
Hot-swap	✓
Easy to install	✓
Country of origin	United Kingdom
Brand compatibility	Brocade

Features	
Certification	CE, FCC, RoHS

Power	
Input voltage	3.3 V
Maximum voltage	3.5 V
Power consumption (typical)	1 W

Operational conditions	
Maximum operating temperature	70 °C
Operating temperature (T-T)	0 - 70 °C
Storage temperature (T-T)	-40 - 85 °C
Operating relative humidity (H-H)	0 - 95%
Storage relative humidity (H-H)	0 - 95%

Weight & dimensions	
Width	13.4 mm
Depth	56.5 mm
Height	8.5 mm
Weight	20 g

Packaging data	
Number of products included	1 pc(s)
Package type	Box

Technical details	
Sustainability compliance	✓
Doesn't contain	Lead
Compliance certificates	RoHS



5056468771377

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 14-OCT-2024. Prints or copies of Information are only valid on the printed Publication date