Part Number : 936014685
Product Description : GWconnect Connector Kit, 32 Pole, Series S-E Female-Male Inserts, Pg36 Extended Threaded Fitting Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 32B «77x62», Grey
Series Number : 93603
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 7932.6753.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93603
Description	GWconnect Connector Kit, 32 Pole, Series S-E Female-Male Inserts, Pg36 Extended Threaded Fitting Die-cast Aluminum Hood-Side Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 32B «77x62», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
UPC	887191865805

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Color - Cable Jacket	N/A
Component Size	32B «77X62»
Lock to Mating Part	Yes
Mounting Style	Bulkhead
Packaging Type	Bag
Thread Size	Pg36
Thread Type	(Pg)