




REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
T		REVISED PER ECO-13-016365	19OCT2013	KH	MZ
U		REVISED PER ECO-19-011232	07AUG2019	RS	MZ
V		REVISED PER ECO-19-014836	18OCT2019	RS	MZ

- 1 HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS.
- 2 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 3 WILL ACCEPT (16) MULTIMATE PIN CONTACTS.
- 4 HOUSING: NYLON, BLUE.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PANEL CUTOUT




5 OBSOLETE	4	STANDARD	ø3.81(.125) HOLES	YES	206036-9-
	4	STANDARD	#4-40 THREADED INSERTS	NO	206036-8
	4	SMALL PACK	ø3.81(.125) HOLES	NO	206036-7
	4	STANDARD	ø3.81(.125) HOLES	YES	206036-4
	4	STANDARD	ø3.81(.125) HOLES	NO	206036-1
MATERIAL		PACKAGING	MOUNTING FEATURES	PERIPHERAL SEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D. GELTZ 07/27/93	TE Connectivity Ltd.	
DIMENSIONS: MM[INCH]			CHK R. STONE 7-22-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD A. FRANTUM 8-12-93	NAME RECEPTACLE HOUSING, STD SEX, SHELL SIZE 17, CPC	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			PRODUCT SPEC 108-10024	SIZE A1	
MATERIAL -			APPLICATION SPEC -	CAGE CODE 00779	
FINISH -			WEIGHT -	DRAWING NO C=206036	
			CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 3
				REV V	

REVISIONS					
#	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT (3) TYPE XII PIN CONTACTS.
- 3



HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.



RECOMMENDED PANEL CUTOUT

PRELIMINARY	3	ø3.18(.125) HOLES	YES	1-206036-6
	3	#4-40 THREADED INSERTS	NO	1-206036-4
	3	ø3.18(.125) HOLES	NO	206036-2
MATERIAL	MOUNTING FEATURES		PERIPHERAL SEAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. GELTZ 07/27/93	TE Connectivity Ltd.	
DIMENSIONS: MM[INCH]		CHK R. STONE 7-22-93		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
		108-10024		
		APPLICATION SPEC		
		SIZE		
		CAGE CODE		
MATERIAL	FINISH	WEIGHT	DRAWING NO	
-	-	-	A1 00779 C=206036	
CUSTOMER DRAWING		RESTRICTED TO		
		-		
		SCALE 2:1 SHEET 2 OF 3 REV V		

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT (16) MULTIMATE PIN CONTACTS.
- 3 HOUSING: NYLON, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
- 4 HOUSING: POLYESTER, PBT, BLACK.
PERIPHERAL SEAL: ELASTOMER, BLACK.
THREADED INSERTS: BRASS



OBSOLETE	4	NO	1-206036-3
	3	YES	206036-5
	3	NO	206036-3
MATERIAL		PERIPHERAL SEAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
D. GELTZ
07/27/93

CHK
R. STONE
7-22-93

APVD
A. FRANTUM
8-12-93

NAME
TE Connectivity Ltd.

DIMENSIONS:
MM[INCH]

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

PRODUCT SPEC
108-10024
APPLICATION SPEC

MATERIAL
-

FINISH
-

WEIGHT
-

CUSTOMER DRAWING

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=206036

RESTRICTED TO
-

SCALE
2:1

SHEET
3 OF 3

REV
V