



产品编号 : [150200101](#)

Product Description : 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 10 Circuits

系列号 : 15020

状态 : Active

Product Category : Flexible Printed Circuit (FPC) Flex Jumpers



文件和资源

图纸


[图纸 150200101_sd.pdf](#)

规格

[产品规格 PS-15020-001-001.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

多部分产品合规性声明

- Eu RoHS
- REACH SVHC
- Low-Halogen

多部分行业合规性文件

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

产品详情

常规

状态	活动
类别	Flexible Printed Circuit (FPC) Flex Jumpers
系列	15020
说明	0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Gold (Au) Plating, 10 Circuits
个评论	Contacts on the same side, Type A
产品系列	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
产品名称	Premo-Flex FFC Jumper
UPC	884982175631

电气

每触点最大电流	0.5A
电压 - 最大	60V AC

物理

电缆长度	102.00mm
回路数 (已载入)	10
触点布局类型	A (same side)
材料 - 接合部位电镀	金牌
净重	0.341/g
包装形式	Bag
间距 - 插配接口	0.50mm
运行温度范围	-40° to +105° C
导线/电缆型号	Flat Flex Cable
线径规格 (AWG)	不适用

可配插部件

描述	产品编号
Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 10 Circuits, Phosphor Bronze, Gold Plating	<u>5019511030</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, V-Flip Series, Vertical, 4.05mm Height, 10 Circuits, Copper Alloy, 125° C Operating Temperature, Gold Plating	<u>5019511050</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, FBH1 Series, Right-Angle, Dual Contact, 1.00mm Height, 10 Circuits, Gold over Nickel Plating	<u>5034801000</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, FD19 Series, Right-Angle, Bottom Contact, 1.90mm Height, 10 Circuits, Gold over Nickel Plating	<u>5051101092</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Vertical, 3.90mm Height, 10 Circuits, Gold Plating	<u>0525591052</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Top Contact, 2.00mm Height, 10 Circuits, Gold Plating	<u>0527451097</u>
Easy-On FFC/FPC Connector, 0.50mm Pitch, Slider Series, Right-Angle, Bottom Contact, 2.00mm Height, 10 Circuits, Gold Plating	<u>0527461071</u>