

Ordering Information:

A3963H-XP - - - -
 1 2 3 4

1.Part No.

2.Material:

(Blank): Nylon 66,UL94V-0(White)

GWT: Nylon 66,UL94V-0(Beige),

IEC 60335-1,5th Edition

Glow Wire Capable.

3.Color:

(Blank): see section 2 Material

BK: Black BR: Brown

RD: Red BL:Blue

4.Logo & Marking:

(blank): Without Mark

CJT: With Mark

SPECIFICATIONS:

Current Rating: 10A AC,DC(AWG #16)

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C





Contact Resistance: 10mΩ Max

Insulation Resistance: 1000MΩ Min


Withstanding Voltage: 1500V AC/minute

Ordering Information & Dimensions


Part NO.	Dimensions(mm)	
	A	B
A3963H-2P	3.96	8.02
A3963H-3P	7.92	11.98
A3963H-4P	11.88	15.94
A3963H-5P	15.84	19.90
A3963H-6P	19.80	23.86
A3963H-7P	23.76	27.82
A3963H-8P	27.72	31.78
A3963H-9P	31.68	35.74
A3963H-10P	35.64	39.70
A3963H-11P	39.60	43.66
A3963H-12P	43.56	47.62
A3963H-13P	47.52	51.58
A3963H-14P	51.48	55.54
A3963H-15P	55.44	59.50



3P~15P



2P



CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	3:1	1 of 1
DRWN	CHK'D	APPR
WennIn Luo	Dtankul Wan	Jack Yin

TITLE
**3.96mm PITCH
 HOUSING**

A3	JL-GC-ECN00771	2025.07.25
A2	CHANGE THE DRAWING	2021.11.03
A1	CHANGE THE DRAWING	2021.03.11
A0	NEW RELEASE	2005.05.10
REV	DESCRIPTION	DATE

General Tolerances
 x.xx±0.25
 x.xxx±0.20
 x.xxxx±0.15
 ANGLES ±1°

THIRD ANGLE
 PROJECTION

DRAWING NO.
A3963H-XP

REV
A3