


Single color electrical schematic diagram  
单色电气原理图



Installation View  
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92211G224GS
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw

**ROCPCU TECHNOLOGY CO.,LTD**

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

性能参数

1. Heating current: Ui: AC250V, Ith: 5A  
发热电流: Ui: AC250V, Ith: 5A
2. Rated current: 3A/DC36V  
额定电流: 3A/DC36V
3. Power-frequency withstand voltage: 2000V1min  
工频耐压: 2000V1min
4. Insulation resistance: ≥1000MΩ  
绝缘电阻: ≥1000MΩ
5. Contact resistance: ≤50mΩ  
接触电阻: ≤50mΩ
6. Pressing stroke: 2.50mm ± 0.10  
按压行程: 2.50mm ± 0.10
7. Contact stroke: 1.50mm ± 0.10  
接触行程: 1.50mm ± 0.10
8. Nut assembly torque: 5-14N  
螺帽装配力矩: 5-14N
9. Protection level: IP67  
防护等级: IP67
10. Explosion prevention level: IK10  
防暴等级: IK10
11. Working environment temperature: -20 °C ~ +55 °C  
工作环境温度: -20 °C ~ +55 °C
12. Compression torque: ≤ 4N  
按压扭力: ≤ 4N

13. Electrical life: 100000 cycles  
电气寿命: 100000 cycles
14. mechanical: 500000cycles  
机械寿命: 500000cycles
15. Operation method: Self compound  
操作方式: 自复式
16. LED lamp power consumption: 20m以下  
LED灯功耗: 20m以下
17. LED lamp lifespan: 40000h  
LED寿命: 40000h
18. LED color: Green  
LED颜色: 绿色
19. LED Lamp Voltage: 24V  
LED灯电压: 24V
20. NO reverse thrust foot torque: ≤30N  
NO反推脚扭力: ≤30N

连接形式

1. Welding temperature of wire: 320 ± 20 °C  
线材焊接温度: 320 ± 20 °C  
Wire welding duration: less than 3 seconds  
线材焊接时长: 时长3秒以下
2. Can be used with dedicated connectors:  
可配专用接插件使用:
  - 2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC)  
开关功能线材: 绿色(C) 蓝线(NO) 黄线(NC)
  - 2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles  
LED功能线材: 红线正极 黑线负极 LED不分正负极

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92211G224GS
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					
A		B		C		D		E		F	

## 材质参数

10	luminous zone 发光区	PC 塑胶	1	
9	LEDpin LED引脚	Brass 黄铜	1	Silvering 镀银
8	Base 底座	PA46	1	
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银
5	LED Base LED基座	PC 塑胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
3	Oring O型圈	Silica gel 硅胶	1	
2	Housing 外壳	SUS 不锈钢	1	
1	Key 按键	SUS 不锈钢	1	
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4			 <p><b>台普</b> <b>ROCPCU</b></p>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3				X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92211G224GS
A2				X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1				X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION DESCRIPTION		ISSUE	ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			