796693-3 ✔ ACTIVE

Buchanan

TE Internal #: 796693-3

Plug, Wire-to-Board, 3 Position, 3.5 mm [.138 in] Centerline, 1 Row, 180° Wire Entry Angle, 30 – 14 AWG Wire Size, PCB Terminal Blocks

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **3.5 mm [.138 in]**

Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Wire Entry Location	Side
Stacking Configuration	Side Stackable
Number of Positions	3
Number of Rows	1
Wire Entry Angle	180°

Electrical Characteristics

Operating Voltage	300 VAC

Body Features

Primary Product Color	Blue

Product Orientation	Right Angle

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11 A

Mechanical Attachment

Screw Plating Material	Nickel
Screw Material	Brass
Thread Size	M2

Housing Features

Housing Material	PA 66
Centerline (Pitch)	3.5 mm[.138 in]

Dimensions

Wire Size	.05 – 2 mm^2

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	200
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (.59% in Component Part) Article Safe Usage Statements:

	Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 284506-3
3 POS TERMI-BLOK PLUG STACK 3,



TE Part # 796694-3
3 POS TERMI-BLOK HDR DIR. POL.



TE Part # 796695-3
3 POS TERMI-BLOK HDR 900 POLAR



TE Part # 284512-3
3 POS TERMI-BLOK HDR 900 POLAR

Customers Also Bought



TE Part #1986693-3
STR PLUG SPRING TYPE LH 3P, 3.50 mm



TE Part #1986718-3
HEADER, 3P, 3.5 PCB 16.5 H WB



TE Part #8-1879512-5
CRGH0805 1% 1M0 0.33W



TE Part #9-1879377-8
CRGH0805 5% 10K 0.33W



TE Part #2118729-2
STD SHIELD COVER, CRS-44.60X31.10X2.00MM



TE Part #2118730-2
STD SHIELD FRAME, CRS-44.00X30.50X3.00MM



TE Part #7-1879496-1
CRGH0805 5% 10M 0.33W



TE Part #206503-1
RECEPT ASSY,62 POSN,AMPLIMITE



TE Part #ADP-RPSM-SMAF-G
RP-SMA Plug to SMA Jack

Documents

CAD Files

Customer View Model
ENG_CVM_CVM_796693-3_B.2d_dxf.zip
English

3D PDF
3D

Customer View Model
ENG_CVM_CVM_796693-3_B.3d_igs.zip
English

Customer View Model
ENG_CVM_CVM_796693-3_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS
English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG
English

Product Specifications

Application Specification
English

Agency Approvals

UL
English