



Material

Insulator: P. B. T. +30%Glass Fiber (UL94V-0)
 Contact: Phosphor Bronze Or Brass
 Contact plated: Gold over Nickel or Tin

Specification

Current Rating: 3A
 Voltage Rating: 250V AC
 Insulator Resistance: 1000M Ω Min. at 500V DC
 Operating Temperature: -55° C ~ +105° C
 Contact Resistance: 15m Ω Max

APPROVED:	DATE:	TITLE: 深圳市灿科盟实业有限公司 CkmtwCHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 2.54短路帽 闭口			
DRAWN:	DATE:	CLIENT P/N	跳线帽	Z-207002P0-0001	
LXF	2009-05-27	UNIT	mm	SCALE	free
TOLERANCE TABLE		FILE NO.	Ckmtw-207-0004	REV.	A
.0	±0.20				
.00	±0.15				
.000	±0.05				