


注: 未经允许禁止传输、复制、编辑该文档, 以及利用其内容进行交流

REV	E.C.N. NO.	CONTENT	CHK	DATE



NOTES1:

UL Standard

Use group	B	C	D
Rated Current	20A	/	/
Rated Voltage	300V	/	/

2.Torque value: M3, 4.43Lb.in

3.Wire range: 22~12AWG

IEC Standard

Pollution Degree	3	2	2
Overvoltage Category	III	III	II
Rate Impulse Voltage(KV)	/	/	/
Rate Voltage(V)	/	400V	/
Rate Current(A)	/	17.5A	/

2. Torque value: M3, 0.5Nm

3.wire range: 2.5mm<sup>2</sup>

NOTES2:

1.Housing: PA66(UL94V-0)

2.Solder Pin: Copper alloy(Sn Plated)

3.Screw: Steel(M3,Ni Plated)

NOTES3:

1.Pitch: 8.25mm Poles: 02 -24P

2.Stripping length: 8mm

3.Operating temperature: -40℃~+105℃

4.RoHS Compliance

How to order

MX35H - 8.25 - XXP - XXXX - XX - X - X

产品型号 间距 颜色: 极数 A-Z其他定制

灰色:GY 橙色:OE 01:常规颜色  
蓝色:BU 红色:RD 02-99:  
黑色:BK 透明色:TT 定制颜色  
绿色:GN 黄色:YW  
透明色:TT 白色:WE

0:Y一字螺丝  
1:S十字螺丝  
2:PS平头十字螺丝  
Cu:铜  
Fe:铁

Pitch Range In mm			Nominal Dimension Range In mm					—	∩	∇
TO	Over 6 TO	Over 10 TO	TO	Over 30 TO	Over 60 TO	Over 100 TO	Over 150 TO	0.1/10	∠	
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00	±1.30	±2°		

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTE
DWG.	CKK	DATE	22.09.14	UNITS	MM SHEET/OF 1/1
CHK.		DATE		SCALE	1:1 A4
APP.		DATE			
				NAME	MX35H-8.25-XXP
				DWGNO.	

CIXI MAIXU ELECTRONICS CO.,LTD.  
慈溪市迈旭电子有限公司