
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
GP	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE	23JAN2007	RG	DO



1. PART NUMBER CHANGES AND OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TYCO APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.

2. MATERIAL:
   POWER INSULATOR - ULTEM 1000, COLOR - BLACK
   SIGNAL INSULATOR - THERMOPLASTIC, GLASS REINFORCED COLOR - BLACK, UL94V-0 FLAMABILITY RATED.
   SOCKET BODY - COPPER ALLOY
   SIGNAL PINS - BRASS ALLOY
   RETENTION CLIP - BERYLLIUM COPPER
   GUIDE PIN - BRASS ALLOY


3. FINISH: GOLD PLATE .000030" MIN THK. OVER NICKEL .000040" MIN THK.
   SOLDER TAILS - TIN .000100 " MIN THK. OVER NICKEL .000040" MIN THK.
   SOCKET BODY - SILVER PLATE .000200" MIN THK. OVER NICKEL .000040" MIN THK.
   GUIDE PIN - PASSIVE

△4 ITEMS PROVIDED TO THIS SPECIFICATION TO NE PERMANENTLY IDENTIFIED PER THE FLOOWING IDENTIFIER:

YEAR ┐ ┌ WEEK

TYCO PART NO. XXXXXXX-X

DATE CODE (e.g. 0425) XXXX



SCALE 1:2

AS SHOWN	6651431-2
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±.3
2 PLC ±.15
3 PLC ±-
4 PLC ±-
ANGLES ±.5

MATERIAL -
FINISH -

DWN 23JAN2007 R.GRZYBOWSKI
CHK 23JAN2007 D.ORRIS
APVD 23JAN2007 S.FLICKINGER
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

tyco Electronics
Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TOP ASSEMBLY, CUSTOM
SOCKET, 72X POWER, 78X SIGNAL
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-6651431	-

CUSTOMER DRAWING | SCALE 3/4 | SHEET 1 OF 1 | REV A