This document was generated on 08/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 2178411123

Status: Active

Overview: Off-the-Shelf Pre-Crimped Leads

Description: Pre-Crimped Lead Mizu-P25 Female-to-Pigtail, Tin (Sn) Plating, 225.00mm Length, 20 AWG, Black



Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Cable Assemblies
Series	217841
Application	Signal, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mizu-P25 Terminal-to-Pigtail
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Mizu-P25
Taxonomy	Power and Signal Cable Assembl
UPC	195842149885

Physical

Cable Length	225.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.590/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.90mm
Wire Size AWG	20
Wire/Cable Type	UL 10002

Electrical

Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing	2178411121-000

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained per - D(2023)3788-DC (14 Jun 2023)

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
217841 Series

Use With
Mizu-P25 2.50mm Pitch Waterproof Receptacle Housing 52213

This document was generated on 08/08/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION