

0401/6401



Basic Part Number	Length A
0401-0	.340
6401-0	.540


X401-0-15-XX-47-XX-04-0
Press-fit in .064 mounting hole

1303




1303-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole

8303



8303-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole


4095



Basic Part Number	Length A
4095-0	.635

409X-0-15-XX-47-XX-04-0
Press-fit in .061 mounting hole


8806



8806-0-18-XX-47-XX-40-0
Surface mount
Also available on 12mm wide carrier tape: 4,000 parts per 13" reel.
Order as: 8806-0-58-XX-47-XX-40-0



P.C.B. Layout



SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: **XXXX - X - 1X - XX - 47 - XX - XX - 0**

BASIC PART #

SPECIFY SHELL FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)



SPECIFY CONTACT FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 27 30μ" GOLD OVER NICKEL (RoHS)

CONTACT

#47 CONTACT (DATA ON PAGE 222)