



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.12.26	阿树
A2	ECN-P-2026031602	Ⓐ2X2	产品尺寸变更	2026.03.16	阿树









P.C.B LAYOUT

Specifications(规格)：
1.Voltage rating(额定电压):250V AC DC
2.Current rating(额定电流):2.0A AC/DC
3.Withstanding voltage(耐压值):≥800V AC/minute
4.Insulation resistance(绝缘电阻):1000MΩ Min
5.Contact resistance(绝缘电阻):20mΩ Max
6.Temperature range(使用温度):-25℃~+85℃

PART NO.:

X2016 W R-05 K-N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

①Series No
②Category:W-Wafer
③Welding Board Angle:R-Stright 90°
④Row No.Pin No:XX-02~20Pin
⑤Special N0:K-Kink; K1-Recerse Kink;
⑥Material:N0-PA66 UL94V-0
⑦Planting: SN-Bright tin plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.00	6.00	12	22.00	26.00
3	4.00	8.00	13	24.00	28.00
4	6.00	10.00	14	26.00	30.00
5	8.00	12.00	15	28.00	32.00
6	10.00	14.00	16	30.00	34.00
7	12.00	16.00	17	32.00	36.00
8	14.00	18.00	18	34.00	38.00
9	16.00	20.00	19	36.00	40.00
10	18.00	22.00	20	38.00	42.00
11	20.00	24.00			

X2016WR-05K-N0SN	PA66 UL 94V-0	BRASS	TIN-PLATED
PART NO.	MATERIAL	MATERIAL(PIN)	FINISH(PIN)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB 星创 Connection

DESIGN	阿树	VIEW:	MODEL TYPE: 2.00mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X2016WR-05K-N0SN
APPROVED		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2