



SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: ≤100mΩ.
3. Insulation resistance: ≥100MΩ (DC250V).
4. Withstanding voltage: 250VAC .
5. Operating Force: 160±50gf/250±80gf (依客户需求而定) .
6. life test: 30,000 cycles.
7. Operation temperature range: -25℃~85℃.
8. Sign"\* "is importance dimension.

				TOLERANCE UNLESS SPECIFIED							
				<1.5: ±0.1mm	ANGULAR	1	2024.2.27	1 按产品更正材质		TQF	
				>1.5~5.0: ±0.25mm	±1°	NO	DATE	REVISIONS		BY	APPD
				>5.0: ±0.3mm							
5	STEM	PA66 1	1	BLACK/WHITE	TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
4	COVER	STAINLESS IRON 1	1	Sn-PLATED	MODEL: TC-00305-050C		SCALE: 1:1		CHK'D		
3	CONTACT	SUS 1	1	Ag-PLATED	DONGGUANG HAOYU ELECTRONICS CO., LTD				APPD		
2	TERMINAL	BRASS 1	1	Ag-PLATED	东莞市弘皓电子有限公司						
1	BASE	PA66 1	1	BLACK	PRO.AGL:						REV: A1
NO.	PART NAME	MATERIAL	QTY	FINISHING							