

PAD AREA

KEEP OUT AREA

RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05

TF CARD PIN DEFINE			
PIN NO.	NAME	TYPE	DESCRIPTION
1	DAT2	I/O/PP	DATE LINE(BIT2)
2	CD/DAT3	I/O/PP	CARD DETECT DATE LIN(BIT3)
3	CMD	PP	COMMAND RESPONSE
4	VDD	S	SUPPLY VOLTAGE
5	CLX	I	CLOCK
6	VSS	S	SUPPLY VOLTAGE GROUND
7	DAT0	I/O/PP	DATE LINE(BIT0)
8	DAT1	I/O/PP	DATE LINE(DIT1)

NOTE:

1.FINISH:

1-1.CONTACT: AU 1U" PLATING ON CONTACT AREA,
100~200U" SN PLATING ON SOLDER TAILS,
50U" NICKEL UNDERPLATING VOER ALL;

1-2.SHELL: NO PLATING;

2.PRODUCT SPECIFICATIONS:


2-1.VOLTAGE RATING: 100V

2-2.CURRENT RATING: 0.5A



2-3.INSULATION RESISTANCE: 1000 MEG.OHM MIN

2-4.CONTACT RESISTANCE: 100 MILL.OHM MAX




2-5.OPERATION TEMPERATURE: -20° TO +85°




制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-TF-1.6HJ	版本 REV.	A
			X.±0.50	X.*±2°	审核 CHECK	EVA	品名 TITLE	T-FLASH CARD HINGED H1.6 螺钉*	页次 SHEET	1/1
			.X±0.30	.X*±1°	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XX±0.20	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1		




1、产品平整包装入载带



天地板



4、装箱



NOTE:

1. QUANTITY/1500 PCS

数量/卷: 1500PCS

2. QUANTITY/INNER CARTON: 1500X11=16500PCS

数量/箱: 1500X10=15000PCS

3. FREE 25 CAVE THE FRONT CARRIER AND FREE 25 CAVE IN THE END CARRIER

包装带内圈空25格, 外圈空25格

3、11 盘整齐叠放, 上下各加一块天地板

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	BX-TF-1.6HJ	版本 REV.	A
			X.±0.50	X.*±2°	审核 CHECK	品名 TITLE	T-FLASH CARD HINGED H1.6 数量T#	页次 SHEET	1/1
			.X±0.30	.X*±1°	核准 APPROVAL	客户料号 CUTM.NO.			
			.XX±0.20	.XX*±0.5°	单位 UNITS	MM		比例 SCALE	1:1

B Bossie (博锡)