





注記
NOTES

- 1.材質
ハウジング：耐熱性ナイロンUL94V-0
ピン：銅合金、ニッケル下地、錫メッキ、金メッキ
フィッティングネール：銅合金、ニッケル下地、錫メッキ
MATERIAL
HOUSING:POLYAMIDE UL94V-0
PIN: COPPER ALLOY, GOLD OR TIN OVER NICKEL PLATE.
FITTING NAIL: COPPER ALLOY, TIN OVER NICKEL PLATE.
- 2.色：ナチュラル、黒、赤、青
COLOR:NATURAL, BLACK, RED, BLUE
- 3.嵌合相手
ハウジング：502351-**0*
錫メッキ端子：50212-8*00,50372-8*00,560085-0101
金メッキ端子：56161-8*81
MATES WITH
HOUSING:502351-**0*
SN PLATING TERMINAL:50212-8*00,50372-8*00,560085-0101
AU PLATING TERMINAL:56161-8*81
- 4.エンボス梱包品の詳細はSD-502352-002参照
DETAILED TAPING PACKAGE, SEE SD-502352-002.
- 5.ELV及びRoHS適合
ELV AND RoHS COMPLIANT
- 6.半田付け面のコプラナリティ：0.1mm MAX.
CO-PLANARITY OF SOLDERING TAILS TO BE 0.1mm MAX.

7.一般公差
GENERAL TOLERANCES
10 UNDER: ±0.2
10 OVER 30 UNDER: ±0.25
30 OVER: ±0.3
ANGULAR: ±3°

INITIAL REVISION:		
DRWN	SHSHIBATA	2007/12/18
CHECK	HKOMATSU	2007/12/18
APPR	AKANESHIGE	2007/12/18

FUNCTIONAL SYMBOLS FA=0 FB=0 FC=0 FD=0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: For fixing wrong view of 6ckt	
	FUNCTIONAL SYMBOLS	DIMENSION UNITS	SCALE	
		mm	5:1	
	GENERAL TOLERANCES (UNLESS SPECIFIED)			
	ANGULAR TOL ± 0.5°			
DIVISIONAL SYMBOLS	4 PLACES	±		
	3 PLACES	±		
	2 PLACES	±		
	1 PLACE	±		
	0 PLACES	±		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES
			A3-SIZE	502352
STATUS: Production		DRWN: Hideo Yoneyama	2024-05-14	DOCUMENT NUMBER
CHK'D: Hiromichi Komatsu		2024-05-16	2024-05-16	
APPR: Takashi Iida				SD-502352-001
		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
		SEE CHART	GENERAL MARKET	1 OF 4



注記
NOTES

1. 製品番号

ナチュラル・錫めっき: 502352-**00

ナチュラル・金めっき: 502352-**10

黒・錫めっき: 502352-**01

赤・錫めっき: 502352-**02

青・錫めっき: 502352-**03

詳細寸法については、製品単体図面を参照下さい。

PART NO.

NATURAL Sn Plating: 502352-**00

NATURAL Au Plating: 502352-**10

BLACK Sn Plating: 502352-**01

RED Sn Plating: 502352-**02

BLUE Sn Plating: 502352-**03


SEE SALES DRAWING FOR CONNECTOR

2. 梱包数量: 700個/リール

NUMBER OF CONNECTORS 700PCS/REEL

3. リードテープ長さ

LEAD TAPE LENGHT



4. 材料

MATERIAL

キャリアテープ: ポリスチレン

CARRIER TAPE: POLYSTYRENE

トップテープ: PET, PE, PEF

TOP TAPE: PET, PE, PEF

リール: ポリスチレン

REEL: POLYSTYRENE

5. 一般公差

GENERAL TOLERANCES

10 UNDER: ± 0.2

10 OVER 30 UNDER: ± 0.25

30 OVER: ± 0.3

ANGULAR: $\pm 1^\circ$

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex				
mm		NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)							2.0MM PITCH W/B CONN. WAFER ASSY EMBOSSED TAPE PACKAGE				
ANGULAR TOL		±	°								
4 PLACES		±									
3 PLACES		±				PRODUCT CUSTOMER DRAWING					
2 PLACES		±									
1 PLACE		±				DOCUMENT NUMBER					
0 PLACES		±									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES	SD-502352-002				
			A3-SIZE	502352							
							DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
							PSD		001	K2	
							MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
							SEE CHART		GENERAL MARKET		1 OF 2

