


A	B	C	D	E		
REV.	DESCRIPTION			ECN NO.	NAME	DATE



适用线路板(PCB LAYOUT)

适用扁平线(Applicable Flat Cable)

序号	品名	材质
1	1.0嵌芯(H2.5)	LCP UL94V-0 本色
2	1.0下端子(H2.5)	铜合金/表面镀锡
3	1.0卧式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0卧式焊片(H2.5)	铜合金/表面镀锡

- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -25°C~+85°C.
 3. 额定电压: 50V, AC/DC.
 4. 接触电阻: $\leq 0.03\Omega$.
 5. 绝缘电阻: $\geq 500M\Omega$

Part No	Pin	A	B	C
FPC-070-S4-FCA	4	3.00	5.03	11.10
FPC-070-S5-FCA	5	4.00	6.03	12.10
FPC-070-S6-FCA	6	5.00	7.03	13.10
FPC-070-S7-FCA	7	6.00	8.03	14.10
FPC-070-S8-FCA	8	7.00	9.03	15.10
FPC-070-S9-FCA	9	8.00	10.03	16.10
FPC-070-S10-FCA	10	9.00	11.03	17.10
FPC-070-S11-FCA	11	10.00	12.03	18.10
FPC-070-S12-FCA	12	11.00	13.03	19.10
.....
FPC-070-S40-FCA	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+6)*1.0+0.10

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.		TITLE: 1.0 Pitch H2.5 ZIF R/A Type Under CONN			
.x	±0.30	DWG. NO.: FPC-070-SX-FCA		CHECKED: MAX	
.xx	±0.20	PART NO.: FPC-070-SX-FCA		DRAWN: ELLA	
.xxx	±0.05	UNIT: mm		APPROVED: WILL	
GENERAL ANGLE:		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
.x'	±5'				
.xx'	±2'				
.xxx'	±1'				

