


RoHS

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.08.14	





3D View



Specifications(规格)：

1.Impedance(特性阻抗)：50Ω；

2.Frequency（工作频率）：DC～6GHz;

3.VSWR （电压驻波比）：1.50 @3GHz；
1.60 @6GHz;

4.Insulation resistance(绝缘阻抗)：≥100MΩ；

5.Dielectric withstand voltage（介质耐电压）：800V AC；

6.Mating cycles（耐久性）：≥25cycles；

7.Retention force latch(保持力)：≥110N；

8.Temperature range(使用温度)：－40℃～+105℃;

9.PART NO.:


XK1PLM1S3－NA26－X

Code: A～Z

10.Housing P/N:


XKHM1－PT26－X

Code: A～Z



RECOMMENDED CABLE STRIPPING DIM'S

BOM List:



NO.	P/N	NAME	MATERIAL	FINISH (Contact)	Q'TY	Note
5	XKS3－BRN01	Outer Ferrule	Copper Alloy	Ni PLATED	1 PC	
4	XKBM3－ZAN221	Outer Conductor	Zinc Alloy	Tin PLATED	1 PC	
3	XKTM3－PBGN601	Center Conductor	Copper Alloy	Gold PLATED	1 PC	5K PCS/R
2	XKHM1－PT26－X	Housing	PBT		1 PC	
1	XKC0－PTY05	Secondary Lock	PBT		1 PC	

www.helloxkb.com www.helloxkb.cn www.xk－dg.cn

ANGLAR	±5°
X.	±0.50
X.x	±0.30
X.xx	±0.15
X.xxx	±0.05
UNSPECIFIED TOLERANCES	















XKB 星坤 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希 文	VIEW:	MODEL TYPE: FAKRA Male Connector for RG174
CHECKED		UNIT: mm/in	PART NO.: XK1PLM1S3－NA26－X
APPROVED		SIZE: A4	DWG NO.: X－XK1PLM1S7－NA26－X

SCALE	PAGE	REVISION
N/A	1/2	A0

Code List:

Colde	 A	 B	 C	 D	 E	 F	 G
Color/RAL-No.	Black/9005	White/9001	Blue/5005	Bordeaux/4004	Green/6002	Brown/8011	Grey/7031
PART NO.	XK1PLM1S3-NA26-A	XK1PLM1S3-NA26-B	XK1PLM1S3-NA26-C	XK1PLM1S3-NA26-D	XK1PLM1S3-NA26-E	XK1PLM1S3-NA26-F	XK1PLM1S3-NA26-G
Colde	 H	 I	 K	 L	 M	 N	 Z
Color/RAL-No.	Violet/4003	Beige/1001	Curry/1027	Carmine red/3002	Pastel Orange/2003	Pastel Green/6019	Water Blue/5021
PART NO.	XK1PLM1S3-NA26-H	XK1PLM1S3-NA26-I	XK1PLM1S3-NA26-K	XK1PLM1S3-NA26-L	XK1PLM1S3-NA26-M	XK1PLM1S3-NA26-N	XK1PLM1S3-NA26-Z

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.15
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB 星坤 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	希 文	VIEW:	MODEL TYPE: FAKRA Male Connector for RG174
CHECKED		UNIT: mm/in	PART NO.: XK1PLM1S3-NA26-X
APPROVED		SIZE: A4	DWG NO.: X-XK1PLM1S3-NA26-X

SCALE	PAGE	REVISION
N/A	2/2	A0

NOTE: ALL RIGHTS RESERVED,BANNED COPY!