






REV.	SPECIFICATION	ECN NO.	APPD.
R6		BCN220049	



Material and plating
Housing: PBT, PA6T, UL94V-0, Black
Contacts: Brass
Gold plated or 80u"min Tin Plated on contact area and
Gold Flash or 80u"min Tin Plated on press fit or solder tail
over Nickel 50u"Min.
Electrical characteristics:
Current Rating: 2 AMP
Dielectric Withstanding Voltage: Ac 1000V for 1 minute.
Insulator Resistance: 1000MΩ min. at DC 500V
Contact Resistance: 20mΩ max. at DC 100mA.
Operating Temperature: -55° C~+105° C
*RoHS compliant
Insertion Depth: 2.55mm to 6.20mm
Ⓢ Important Dimensions



Series 2044 - 2 X xx G xx S A
A: Tray Package
S: Straight
Pin number of each row: xx
00: Gold Flash
10: 10u"
15: 15u"
30: 30u"
Blank: for Copper Plated
G: Gold Plated
T00: Copper Plated

Tolerances	Dwg. No.	2044-D0000-003	
x = ±0.5	Projection	⊕ ◀	
.x = ±0.25	Unit	mm	Scale 1:1
.xx = ±0.15	Drawn By	ZY 08/23'22	

Title:
2044系列 双排排母 间距
2.54mm 2XNP 直插 H=8.5 PC3.2
PBT Y型 镀金GF

WINGTAT
深圳市格林柏电子技术开发有限公司
P/N: 2044-2XxxGxxSA
SHBET 1/1 **Ver. No.** R6