



Recommended P.C.Board Layout

SPECIFICATIONS

Current Rating:2.0AMP
 Contact Resistance:30mΩ Max
 Insulation Resistance:1000MΩ Min
 Withstand Voltage:500V AC/minute
 Operation Temperature:-40°C to +105°C
 Contact Material: Brass
 Contact Plating:Au or Sn over 50 μ "Ni
 Insulator Material:Polyester(UL94V-0)
 Standard:Nylon - 6T

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	C_{kmtw} 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO.,LTD					
CHECKED:	DATE:	TITLE: 220-2R-1*XP H=4.3 U型端子 (弯排母)					
DRAWN: SXA	DATE: 2023-11-23	CLIENT P/N		/			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-220-20017	REV.	B	/	