





未注公差/General tolerances(mm)

0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10 ±2'
~3	~6	~10	~18	~30	~50	~80	~120	~180	~250	~315	~400	~500		
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

REV	ECN	DESCRIPTION	DRFT	DATE



PCB Layout



DB2ERH — 2.5 — XXP — C
 (Series No.) (Pitch) (Poles)

(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)
 OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

UL 标准/UL Standard:	B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)	150/5	/	/
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree	III/3	III/2	II/3
额定电压/电流/Rated Voltage(V)/Current(A)	80/6	160/6	320/6
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	2.5	2.5	2.5
螺丝扭矩/Torque Tightening(N·m/Lb.in)		/	
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm ² /AWG)		/	
间距/Pitch(mm)/线数范围/Poles	2.5/N=02-24		
剥线长度/Stripping length(mm)		/	
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		

Pin 2	Copper alloy	Sn Plated
Pin 1	Copper alloy	Sn Plated
Housing	PA66	UL94V-0
NAME OF PART	MATERIAL	NOTES

MAT NO.:	/	宁波地博电气有限公司 NINGBO DORABO ELECTRICAL CO., LTD
STATUS:	/	
APPD: J.Ting Chen 2024.09.21	NAME:	DB2ERH-2.5-XXP-C
CHKD: Duck Mao 2024.09.21	DRAWING NO.:	/
DRFT: Steven Lu 2024.09.21	REV	M1
SIZE: A4	TYPE: CUSTOMER_DRAWING	SCALE: 1:1
mm (inch)	SHEET	1/1