


PIN RECEPTACLES

FOR 0,56 - 0,81 DIAMETER PINS

0295

0295-0-15-XX-06-XX-10-0


Solder mount in 1,60 min. mounting hole
Also available on 24mm wide carrier tape:
1,000 parts per 330mm reel
Order as: 0295-0-57-XX-06-XX-10-0



0292

0292-0-15-XX-06-XX-10-0


Solder mount in 1,8 min. mounting hole



0294

0294-0-15-XX-06-XX-10-0


Solder mount in 1,93 min. mounting hole



0398

0398-0-15-XX-06-XX-04-0


Press-fit in 1,68 mounting hole



0397

0397-X-15-XX-06-XX-04-0

Press-fit in 1,68 mounting hole




Basic Part Number	Length V
0397-0	8,97
0397-1	8,46
0397-2	10,49

0297

0297-0-15-XX-06-XX-04-0


Press-fit in 1,7 mounting hole



9019/9039

90X9-0-19-XX-06-XX-10-0

Press-fit in 1,91 mounting hole



Basic Part Number	Head Dia. C
9019-0	3,18
9039-0	2,54

SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 06 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 15 0,25µm GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01 5,08µm TIN/LEAD OVER NICKEL
- ◆ 80 5,08µm TIN OVER NICKEL (RoHS)
- ◆ 27 0,76µm GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#06 CONTACT (DATA ON PAGE 255)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com