



STRUCTURE (构造)			
NO.	ITEM (项目)	SPECIFICATION (规格)	
1	INSULATION (胶膜)	印字膜:通用版20624 (43μm)	
		白膜:80° C 60V (43μm)	
2	SUPPORTING TAPE (补强板)	225μm	Blue (蓝色)
3	CONDUCTOR (导体)	Thickness (厚度)	0.035 ±0.005
		Width (宽度)	0.65 ±0.03
4	CONDUCTOR (导体镀层)	PLATED (电镀)	锡Sn (1μm) MIN
		PLATED (电镀)	

DIMENSION (尺寸)			
No. of conductors (导体数目)	N	(N) P	
Pitch (间距)	P	1.0	±0.08
Span (总间距)	SP	(N-1)*1	±0.1
Width (总宽度)	W	(N+1)*1	±0.12
Margin (边缘宽度)	M	1.0	±0.12
Total length (总长度)	TL	(TL)	±2.0
Insert Thickness (插接端厚度)	T	0.3	±0.03
Surface Thickness (线身厚度)	ST	0.121	±0.03
Strip Length (裸铜长度)	S1	4.0	4/3可定做 ±0.5
	S2	4.0	4/3可定做 ±0.5
Supporting Tape Length (补强板长度)	B1	8.0	8/6/5/4/可定做 ±1.0
	B2	8.0	8/6/5/4/可定做 ±1.0

技术要求:

- 1、保存环境: 温度 15~25℃ 湿度: 30~50RH%
- 2、保质期: 镀金: 12个月 镀锡: 6个月
- 3、产品符合RoHS 2.0标准

DESIGN:	Xiping Huang			广东国连电子有限公司	
CHECK:	Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO., LTD	
APPROVED:	Youquan Xu		TITLE: FFC CABLE B型		
DIM	TOL	DIM	TOL	PART NO. 1.0*NP*TL*B (3/3/5/5) (0.035*0.65)	
X.	±0.25	X°	±3.0°	REV. A	SCALE: N/A
X.X	±0.20	X.X°		UNIT: mm	SHEET: 1/1
X.XX	±0.15	X.XX°			
X.XXX		X.XXX°			