











脚位尺寸以过孔规为准



PCBLAYOUT TOP VIEW
TOL:±0.05

NOTES:

1. HOUSING MATERIAL:GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL:PHOSPHOR BRONZE.
3. PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
4. SHELL:BRASS,T=0.20. WITH 40u" NICKEL PLATED.

ELECTRICAL:

1. VOLTAGE RATING: 125V AC RMS.
2. CURRENT RATING: 1.5AMP.
3. CONTACT RESISTANCE: 30MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500MEG OHMS MIN @500V DC.

MECHANICAL:

1. DURABILITY: 750 CYCLES MIN.
2. INSERTION FORCE : 22N MAX.
3. REMOVAL FORCE(WITHOUT PLUG LOCK) : 22N MAX.

ENVIRONMENTAL:

1. STORAGE: -40°C~85°C
2. OPERATION: -40°C~85°C

*Apply to the EU standards(ROSH)

1. ①~⑨ FOR QIP DIM.

3003 - 0 05 - XX

系列码

类别码

05:DIP铜壳无灯

流水码

11:GF LCP黑 盘装

21:GF LCP黑 卷装

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.35	UNIT		MM		www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.XX	±0.25	SIZE	A4	DESIGN	赵文品2024.11.06	PART NO.	RJ45-3004-005-11		
				X.XXX	±0.05	SHEET	1/1	CHECK		TITLE:	RJ45 沉板4.2 DIP有壳无灯GF LCP黑		
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DATE	TOL	PROJ.		APPROVE		Customer No.			