

Specification Sheet

Part Number: MB20M4



For use with 18 through 50 pound cable ties to provide stability when securing bundles.

Low profile design offers use in space constrained areas.

Secures with a single screw providing quick installation.

Cable Tie Anchor Mount, 0.81 x .49", 0.193" Hole Dia, 0.18" Max Tie Width, PA66, Black, 1000/pkg

Article Number 151-00301

Type MB2

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton cable tie screw mounts are used with 18 through 50 pound cable ties to provide stability when securing bundles. The low profile design allows for use in space constrained areas. The mounts are installed quick and easy by securing a single screw.

Short Description Cable Tie Anchor Mount, 0.81 x .49", 0.193" Hole Dia, 0.18" Max Tie Width, PA66, Black, 1000/pkg

Global Part Name MB2-PA66-BK

Length L (Imperial)	0.81
Length L (Metric)	20.6
Fixation Method	Screw Mount
Width W (Imperial)	0.49
Width W (Metric)	12.5
Cable Ties	T18 - T50
Height H (Imperial)	.13
Height H (Metric)	3.30
Cable Tie Width Max (Imperial)	0.18
Cable Tie Width Max (Metric)	4.6
Mounting Hole Diameter D (Imperial)	0.193
Mounting Hole Diameter D (Metric)	4.9 mm
Mounting Hole Diameter D Max (Metric)	4.9
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)