





TABLE 1

SUB ASSEMBLY PART NO.	NO.	PART NO.	MATERIAL	COLOR	QTY.
7282-1248 ETC.	①	SEE TABLE 2	② PBT	SEE TABLE 2	1
	②	7157-4053	② PBT	NATURAL	1

TABLE 2

SUB ASSEMBLY PART NO.	PART NO.	COLOR
7282-1248, Ⓐ	7182-1248	NATURAL
7282-1248-10, Ⓐ	7182-1248-10	DARK GRAY
7282-1248-30, Ⓐ	7182-1248-30	BLACK
7282-1248-40, Ⓐ	7182-1248-40	LIGHT GRAY
7282-1248-50, Ⓐ	7182-1248-50	ORANGE
7282-1248-60, Ⓐ	7182-1248-60	GREEN
③ 7282-1248-70, Ⓐ	7182-1248-70	YELLOW
① 7282-1248-80, Ⓐ	7182-1248-80	BROWN
7282-1248-90, Ⓐ	7182-1248-90	BLUE

注記

③ 1. 取扱説明書No. : YPES-15-080, YPES-15-125

① 2. かん合相手品番 :7283-1248 ETC.

NOTES

③ 1. HANDLING MANUAL NO. : YPES-15-080, YPES-15-125

① 2. MATING PART NO. :7283-1248 ETC.

ISSUE MARK

LET	DATE	REVISION RECORD	NO.	CHKD
③	12.04.19	ADDED PART NO. ETC.	C12-Z396	G.M
②	97.12.11	CHANGED MATERIAL	C97-N742	H.K
①	96.07.05	CHANGED MATERIAL, Ⓐ	C96-M147	H.K
	92.05.29	NEW	C92-L427	T.T

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30′	0.1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30′	0.1
Ⓒ	±0.3	±0.5	±0.8	±1.4	±2	±30′	0.15

SPECIFIED MASS

CUSTOMER

CUSTOMER PART NO. CUSTOMER DWG NO.

OFFICE TRIAL PART NO.

VENDOR

VENDOR NO.

DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
R	NEW	92.05.29	mm	2/1	3

APPROVED	CHECKED	CHECKED	DESIGN	DRAWN
M. FUKUDA	T. HIRAKAWA	A. TASHIRO	Y. OHTA	G. MAGNAYON
12.04.19	12.04.19	12.04.19	89.05.20	12.04.19

MATL. SPEC. SEE TABLE 1 TREAT. & FIN.

NAME ③ 2.3II 20P+4.8 4P HYBRID HOUSING SUB ASSEMBLY MALE

PART NO. 7282-1248 ETC.

CH. CODE

DWG NO. 7282-1248:R SET DWG NO.

YAZAKI CORPORATION