


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30DEC2016	DL	CW
	A1	ECR-16-018258	30DEC2016	BS	CW
	B	ECR-18-016391	22OCT2018	GY	CW
	C	ECR-20-014876	21JUL2021	WQR	CW


TYPE I: HIGH CONSTRUCTION + STATINLESS STELL LOCKING.
类型Ⅰ：高结构+不锈钢双扣。














NOTES:

1. TECHNICAL CHARACTERISTICS:
   HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY
   HOUSING SURFACE: POWDER COATED, GREY
   DEGREE OF PROTECTION: IP65 (MATED)

注释：
1. 技术参数：
   下壳材料： 铝合金
   下壳表面处理： 灰色粉末喷涂
   防护等级： IP65(配合)

PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD-1 螺纹孔-1	PG/M THREAD-2 螺纹孔-2	TYPE 类型
TI470241121-000	H24B-SGRHS-PG21 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，PG21，高结构，灰色粉末喷涂	PG21	-	TYPE I 类型I
TI470241129-000	H24B-SGRHS-PG29 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，PG29，高结构，灰色粉末喷涂	PG29	-	
TI470241132-000	H24B-SGRHS-M32 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，M32，高结构，灰色粉末喷涂	M32	-	
TI470241221-000	H24B-SGRHS-2PG21 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，2PG21，高结构，灰色粉末喷涂	PG21	PG21	
TI470241229-000	H24B-SGRHS-2PG29 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，2PG29，高结构，灰色粉末喷涂	PG29	PG29	
TI470241232-000	H24B-SGRHS-2M32 H24B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，不锈钢双扣，2M32，高结构，灰色粉末喷涂	M32	M32	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: TBD -
FINISH: - -

DWN DAVID LI 17JUN2015
CHK CHRIS WANG 17JUN2015
APVD XU XIANG 17JUN2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H24B-SGRHS-PG/M


SIZE A2 | CAGE CODE - | DRAWING NO C-T147024XXXX000 | RESTRICTED TO


CUSTOMER DRAWING | SCALE 4:5 | SHEET 1 OF 2 | REV C


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

TYPE 2: HIGH CONSTRUCTION + STELL LOCKING, OTHER SPEC REFER TO TYPE 1.
类型2：高结构+彩锌双扣，其他规格参照类型1.











PG/M
THREAD-2
螺纹孔-2

PG/M
THREAD-1
螺纹孔-1



PG/M
THREAD-3
螺纹孔-3



NOTES:
SEE SHEET 1

PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD-1 螺纹孔-1	PG/M THREAD-2 螺纹孔-2	PG/M THREAD-3 螺纹孔-3	TYPE 类型
T1470242121-000	H24B-SGRH-PG21 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG21，高结构，灰色粉末喷涂	PG21	-	-	TYPE 2 类型2
T1470242125-000	H24B-SGRH-M25 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M25, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M25，高结构，灰色粉末喷涂	M25	-	-	
T1470242129-000	H24B-SGRH-PG29 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG29，高结构，灰色粉末喷涂	PG29	-	-	
T1470242132-000	H24B-SGRH-M32 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M32，高结构，灰色粉末喷涂	M32	-	-	
T1470242221-000	H24B-SGRH-2PG21 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG21，高结构，灰色粉末喷涂	PG21	PG21	-	
T1470242225-000	H24B-SGRH-2M25 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M25, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2M25，高结构，灰色粉末喷涂	M25	M25	-	
T1470242229-000	H24B-SGRH-2PG29 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG29，高结构，灰色粉末喷涂	PG29	PG29	-	
T1470242232-000	H24B-SGRH-2M32 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2M32，高结构，灰色粉末喷涂	M32	M32	-	
T1470242921-000	H24B-SGRH-PG21/PG29 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG21/PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG21/PG29，高结构，灰色粉末喷涂	PG21	PG29	-	
T1470242932-000	H24B-SGRH-PG29/M32 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG29/M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，PG29/M32，高结构，灰色粉末喷涂	PG29	M32	-	
T1470243216-000	H24B-SGRH-M32/MI6 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M32/MI6, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，M32/MI6，高结构，灰色粉末喷涂	M32	MI6	-	
T1470242229-001	H24B-SGRH-2PG29/M32 H24B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG29, BOTTOM ENTRY M32, HIGH CONSTRUCTION, POWDER COATED, GREY H24B下壳，表面安装，彩锌双扣，2PG29，底出M32，高结构，灰色粉末喷涂	PG29	PG29	M32	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL: TBD -
FINISH: - -

DWN DAVID LI 17JUN2015
CHK CHRIS WANG 17JUN2015
APVD XU XIANG 17JUN2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H24B-SGRH-PG/M

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	C-T147024XXXX000	

CUSTOMER DRAWING | SCALE 1:2 | SHEET 2 OF 2 | REV C