

2203232-4 ✔ ACTIVE



AMP | FAKRA RF Connector System

TE Internal #: 2203232-4

TE Internal Description: SOCKET CONTACT, PLUG, 180 DEGREE, SMB

View on TE.com >

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1-2035141-0
PLUG KIT, 90 Deg, RG-316 or -174, Fakra



TE Part # 2151839-1
OCEAN-2.0-APPLICATOR-S-047F-SSM



TE Part # 5-2138895-1
PLUG KIT, UNASM, 1 POS, RG-174, HD, A,CS



TE Part # 7-2151839-7
OCEAN_2.0_SPARE_PART_KIT-047F



TE Part # 2266955-1
OCEAN_2.0_APPLICATOR-S-046F-RSM



TE Part # 5-1438911-7
JACK KIT, UNASSEM, 1 POS, KEY F, CLP SLT

TE Part # 2374847-1
CD542 FAKRA AUT CABLE ASSY

TE Part # 2374847-4
CD542 FAKRA AUT CABLE ASSY

TE Part # 2374847-2
CD542 FAKRA AUT CABLE ASSY

TE Part # 2374847-3
CD542 FAKRA AUT CABLE ASSY



TE Part # 2151839-2
OCEAN-2.0-APPLICATOR-S-047FA-SSA



TE Part # 2266776-2
OCEAN_2.0_APPLICATOR-S-042F-SSA



TE Part # 1924792-9
PLUG KIT, UNASSEM, 1 POS, RG174 KEY I



TE Part # 5-2138894-4
PLUG KIT, UNASM, 1 POS, RG-58, HD, D,CS



TE Part # 2266955-2
OCEAN_2.0_APPLICATOR-S-046F-RSA



TE Part # 2266775-1
OCEAN_2.0_APPLICATOR-S-046F-RSM



TE Part # 2035141-3
PLUG KIT, 90 Deg, RG-316 or -174, Fakra



TE Part # 1924792-6
PLUG KIT, UNASSEM, 1 POS, RG-316 OR RG-1




TE Part # 2266775-2
OCEAN_2.0_APPLICATOR-S-046F-RSA




TE Part # 2266776-1
OCEAN_2.0_APPLICATOR-S-042F-SSM

Also in the Series | FAKRA RF Connector System



Automotive Connector EMC Shielding (3)



Automotive Connector Locks & Position Assurance(8)




Automotive Headers(2)




Automotive Housings(5)




Coax Connectors(1)




Data Connectivity Headers(367)



Infotainment & Multimedia Cable Assemblies(1)




Other Automotive Connector Accessories(26)



Wire-to-Board Headers & Receptacles (1)

Customers Also Bought




TE Part #154717-6

PL 250 REC TERMINAL 14-11 AWG PTPB



TE Part #1924791-1

PLUG SUBASSEMBLY, RG-316 OR RG-174



TE Part #2138495-1

PLUG HOUSING, 1 POSITION, FAKRA, Key A



TE Part #776760-1

End Cap, 1 POS, RG-174, 90 DEG, FAKRA



TE Part #1488499-3

FERRULE,NI PLT,RG58,FAKRA



TE Part #2138981-1

PLUG SUBASSEMBLY, 1.5DS-QFB, FAKRA



TE Part #2138982-1

JACK SUBASSEMBLY, 1.5DS-QFB, FAKRA



TE Part #2203238-1

PLUG SUBASSEMBLY, RTK031 2DS-PPFW, FAKRA



TE Part #2291354-1
PLUG SHELL BOTTOM, 0.50 HSL CONNECTOR

TE Part #7-2836899-7
OCEAN_2.0_SPARE_PART_KIT-134O

Documents

Product Drawings

SOCKET CONTACT, PLUG, 180 DEGREE, SMB

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2203232-4_A_c-2203232-4-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2203232-4_A_c-2203232-4-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2203232-4_A_c-2203232-4-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English