

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:30mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c

Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Resistance To Soldering Heat:

245°C±5°C, 10s(PBT insulator)


Dimension antitheses list	
ITEM	A
Standard	2.90

Ordering Information

HC-CZ 254 - * - N - W - * - ** - *		No. of Rows	No. of Pins	Type	Length (Plastic)	Contact Plating	Contact Type
		2= Dual Row	10/16/20Pin	0=100°	32/44/48Pin	G0:Gold Flash	F=Female
		3= Three Row	32/44/48Pin	90°	64Pin	G1:1u" Gold	M=Male
		4= Four Row	64Pin	180°		G2:3u" Gold	
						G3:5u" Gold	
						G4:10u" Gold	
						G5:15u" Gold	
						G6:30u" Gold	
						S0:Gold Flash/Tin	
						S1:Tin	

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO., LTD

产品名称 TITLE	版 本 REV.	单 位 UNITS	页 次 SHEET
欧式插座2.54 双排 弯公座	A	mm	1/1
产品料号 PART NO.	HC-CZ254-2-N-W-13.0-XX-M		
材 料 MATERIAL			



GENERAL TOLERANCE			制 图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
DIM			TOL		审 核 CHECK			
X. X			± 0.30		批 准 APPROVAL			
X. XX			± 0.20		比 例 SCALE			
X. XXX			± 0.10		投 影 Projection			
Angle			$\pm 3.0^\circ$					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						
1	初版发行							