



SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30-60seconds
 (260° C for 5seconds)

P/N	PIN	DIM. A	DIM. B
HMT-2.54-1*1PM	1	0.00	2.54
HMT-2.54-1*2PM	2	2.54	5.08
HMT-2.54-1*3PM	3	5.08	7.62
HMT-2.54-1*4PM	4	7.62	10.16
HMT-2.54-1*5PM	5	10.16	12.70
HMT-2.54-1*6PM	6	12.70	15.24
HMT-2.54-1*7PM	7	15.24	17.78
HMT-2.54-1*8PM	8	17.78	20.32
HMT-2.54-1*9PM	9	20.32	22.86
.....
HMT-2.54-1*40PM	40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.±0.30	X.°±5°	PART NO.	TITLE: 2.54FH H8.5 1xnPin		
.X±0.20	.X°±1°	HMT-2.54-1*NPM	180度 Y型 PC3.2 6T		
.XX±0.10	.XX°±0.5°	DESIGN: James	CUSTOMER	SIZE	
MANUFACTURE DWG		CHED: Talen		A4	UNITS
		APPD: Sophia		SCALE	SHEET
				N:A	1/1