








NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
   PLATING: GOLD FLASH over NICKEL
   SOLDER CUP ACCEPTS CABLE AWG 20
4. HIGH POWER CONTACTS 20A: COPPER ALLOY
   PLATING, MATING AREA: GOLD FLASH over NICKEL
   PLATING, TERMINATION SIDE: GOLD FLASH over NICKEL
   SOLDER CUP ACCEPTS CABLE AWG 12-14
5. CONNECTOR IS PART MARKED: 3013W3SAM62A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Original		

tolerance: dim. in mm

	date	name
drawn	23.09.13	Lehmenkühler
appd.	23.09.13	Koch
norm		
d-old		

scale: 2:1 (5:1)

material: SEE NOTES

title: D-SUB COMBINATION FEMALE
13W3S SOLDER CUP

dwg no: 13K1A4466

DIN-A3

sh: 1

part no: 3013W3SAM62A10X