





REV.	ECN NO.	REVISED	DATE



技术要求:

- 1、截剪断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;
- 3、冲压后,产品先热处理,处理后产品要有足够弹性强度,则同时还要有一定韧性;

1	TERMINAL	1	STAINLESS STEEL T=0.30mm	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2023-05-12	TITLE:	
X : ±0.30	X : ±1°	CHKD	ZhouRuicai	DATE	2023-05-12	电池弹片CR123A Ni DIP	
X.X : ±0.25	X.X : ±0.5°	APVD	XueShunyong	DATE	2023-05-12	PART NO.:	
X.XX : ±0.20						MY-123A-01-J	
X.XXX : ±0.10						DRAW NO.:WD-CP-0169	
WEIGHT:		SCALE:	SIZE: A4	VIEW:	⊙ ⊞		
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY			