


REV. 0
DCO 140945

COIL: @ 25°C

RESISTANCE	3300 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.2 VDC
TURN-ON BASE CURRENT	0.06 mADC
MUST RELEASE	8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:


VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION

TEMPERATURE -65 °C TO +125 °C

NOTES: TURN-ON TIME 4.0 MS MAX
TURN-OFF TIME 7.5 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/4/99 CK. 3-4-99

COMMUNICATIONS INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M28776/3-046L

TYPE JMST RELAY

JMSCT-26XLS