


REV. 1
DCO 102710

COIL: @ 25°C


RESISTANCE	58-83 OHMS
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	6.5 VDC
MUST RELEASE	3.6 VDC MAX, 0.8 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
SHOCK 50 g's 11 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 15 MS MAX.
OPERATE BOUNCE 5 MS MAX.
RELEASE BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: 10 AMPS 28 VDC
5 AMPS 115 VAC/400 Hz RESISTIVE
50,000 OPERATIONS

DR. RB 3/9/98 | CK. TLG 8-17-01

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M5757/23-009 REV.

"07" RELAY

B07D934BB2-0119

F-718 REV. 3