

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A1	N/A		尺寸修正, 料号变更, 图框升级整理图面	2024.08.15
A2	N/A		产品总长尺寸修正	2024.08.20


SPECIFICATIONS
Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-45°C~+125°C
Contact Material:Phosphor Bronze
Contact Plating:Au Plating and Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30~60 seconds
(260°C for 10 seconds)

PART NO.:
X4611 F V S-XX-C43 D45 X X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
② Category:T-Terminal
③ Welding Board Angle:V-Stright 180°
④ Welding Way:S-SMT
⑤ Row No.Pin No:XX-02~40Pin
⑥ Plastic Height:C=4.3mm
⑦ Pin pitch:D=4.5mm
⑧ Planting Categoty:Blank=gold plating 1U''
SN=Plating Tin
AuSn=Terminal half-AuSn
V03=Plating 3U''
V15=Plating 15U''
V30=Plating 30U''
⑨ Type:R1 ; R2

X4611FVS-XX-C43D45XX	PA6T	Brass	X4611W
PART NO	Material	Wire Range	Suitable XKB Wafer


ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	




DESIGN	阿 树	UNIT: mm/in SIZE: A4	MODEL TYPE: 2.00mm BTB Connectors
CHECKED			PART NO.: X4611FVS-XX-C43D45XX
APPROVED			DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED


SCALE	PAGE	REVISION
N/A	1/1	A2




TYPE01



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



TYPE02



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

