

SPECIFICATIONS

Current Rating:1.0 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:-40° to+105°

Insulator Material:Polyester(UL94V-0)




Contact Material:Brass

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ1.27VS-02-01P	2*1	0.00	1.27
XY-PZ1.27VS-02-02P	2*2	1.27	2.54
XY-PZ1.27VS-02-03P	2*3	2.54	3.81
XY-PZ1.27VS-02-04P	2*4	3.81	5.08
XY-PZ1.27VS-02-05P	2*5	5.08	6.35
XY-PZ1.27VS-02-06P	2*6	6.35	7.62
XY-PZ1.27VS-02-07P	2*7	7.62	8.89
XY-PZ1.27VS-02-08P	2*8	8.89	10.16
XY-PZ1.27VS-02-09P	2*9	10.16	11.43
.....			
XY-PZ1.27VS-02-50P	2*50	(PIN-1)x1.27	(PIN)x1.27

RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*± 5°	APR.	Alex	TITLE: 1.27PH H1.0 2xnPin SMT W3.4 PC5.5 PA4.0 PB1.5 L7.2 6T	
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. XY-PZ1.27VS-02-NP	
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1