


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE








SPECIFICATION:
- Current Rating: 2AMP
- Temperature Range: −40℃to+105℃
- Contact Resistance: 20mΩ Max
- Insulation Resistance: 1000MΩ Min
- Withstanding Voltage: AC 500V

Material:
- Insulator: Polyester (UL94V−0)
- Standard: PA9T
- Contact: H65
- Plating: Au over Ni



COSTOMER DRAWING			
DRAWING			
CHECKED			
APPROVED			
TOLERANCES ARE			
30-150	±0.35	ANGLE	
10-30	±0.2		
5-10	±0.15	±3°	
0-5	±0.1		

LAILAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
TITLE	排母 PIN距2.0 塑高4.3 双排2PIN直插	REV.	A
PART NO.	LAIL-PM2.0-2PX2-L	UNITS	mm
DWG. NO.		Projection	