This document was generated on 02/27/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0150140261

Status: Active

Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers

Description: 0.25mm Pitch Premo-Flex FPC Jumper, Same Side Contacts (Type A), 51.00mm Cable Length, Gold (Au) Plating, 61 Circuits



Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
Product Specification 1501400001-000 (PDF)
RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15014
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
Taxonomy	Flexible Printed Circuit (FPC)
UPC	191130093274

Physical

Cable Length	51.00mm
Circuits (Loaded)	61
Contact Layout Type	A (same side)
Material - Plating Mating	Gold
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Mating Interface	0.25mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flexible Printed Circuitry

Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	N/A

Material Info

Reference - Drawing Numbers

Product Specification	1501400001-000
Sales Drawing	150140001-000

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Reviewed
Halogen-Free Status
Not Reviewed
For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
15014 Series

Mates With
Easy-On FPC Connector 5020786162

This document was generated on 02/27/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION