





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




SPECIFICATIONS

- 1.CURRENT RATING: 0.3A .
- 2.VOLTAGE RATING 30V AC/DC.
- 3.TEMPERATURE RANGE:-35°C TO +85°C
- 4.CONTACT RESISTANCE: 90mΩ MAX.
- 5.INSULATION RESISTANCE:50 MΩ MIN.
- 6.WITHSTANDING VOLTAGE:100V AC/MINUTE.



The product is high



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ±0.05

PIN	A	B	C
JXT-10DP-0415	3.52	1.6	1.0
JXT-12DP-0415	3.92	2.0	
JXT-20DP-0415	5.52	3.6	
JXT-24DP-0415	6.32	4.4	1.2
JXT-30DP-0415	7.52	5.6	1.5
JXT-34DP-0415	8.32	6.4	2.3
JXT-40DP-0415	9.52	7.6	3.2
JXT-44DP-0415	10.32	8.4	
JXT-50DP-0415	11.52	9.6	
JXT-60DP-0415	13.52	11.6	
JXT-70DP-0415	15.52	13.6	
JXT-80DP-0415	17.52	15.6	
JXT-90DP-0415	19.52	17.6	
JXT-100DP-0415	21.52	19.6	

The product is high

The product is high	H
JXT-NDP-0415	1.45
JXT-NDP-0420	1.95
JXT-NDP-0424	2.40
JXT-NDP-0429	2.90
JXT-NDP-0434	3.40
JXT-NDP-0439	3.90

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.±0.50	X.*±2°	PART NO.	TITLE:
X.X±0.35	X.X*±1°	JXT-NDP-0415	0.40MM BTB PLUG
X.XX±0.25		DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	SCALE SHEET N:A 1/1
MATERILA	---	APPD: Ava	
FINISH	---		