





Shipping Arrangement:50 sets per strip
Shipped in carton box







Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:2A AC/DC
额定电流：2A AC/DC
Withstanding voltage:1200V AC/minute
耐受电压：1200V AC/分钟
Temperature range:-40℃-+125℃
温度范围：-40℃-+125℃
Insulation resistance:1000MΩ min
绝缘电阻：1000MΩ Min
Contact resistance:10mΩ Max
接触电阻：10mΩ Max





SEC:E-E






SEC:F-F







X25061 H I - 04 A 00 - PT SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No
2.Category:H-HSG
3.Category:I-Punctured type
4.Row No.Pin No:XX-02~17 Pin
5.Appearance type:A Type
6.Spacer bar:For example12-Keying between pin 1 and pin 2
23-Keying between pin 2 and pin 3...When the pin number is above 10,use the letters A ,B C...A for 10,B for 11...
Blank-No Keying
7.Material:PT-PBT ;N0-PA66 UL 94V-0
8.Platig:SN-Plated Tin ; V01-Gold Flash;V03-Gold 3u;
V15-Gold 15u;V30-Gold 30u

Poles	Dimensions(mm)	
	A	B
02	7.40	2.50
03	9.90	5.00
04	12.40	7.50
05	14.90	10.00
06	17.40	12.50
07	19.90	15.00
08	22.40	17.50
09	24.90	20.00
10	27.40	22.50
11	29.90	25.00
12	32.40	27.50
13	34.90	30.00
14	37.40	32.50
15	39.90	35.00
16	42.40	37.50
17	44.90	40.00

Spacer bar	C	D
00	/	/
12	7.40	2.50
23	9.90	5.00
34	12.40	7.50
45	14.90	10.00
56	17.40	12.50
67	19.90	15.00
78	22.40	17.50
89	24.90	20.00
9A	27.40	22.50
AB	29.90	25.00
BC	32.40	27.50
CD	34.90	30.00
DE	37.40	32.50
EF	39.90	35.00
FG	42.40	37.50
GH	44.90	40.00

X25061HI-04A00-PTSN	AWG24~22	Phosphor	X25061W
PART N0	Wire Range	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Pitch Rast Connector
DWN		VIEW:	PART NO.: X25061HI-04A00-PTSN
CHKD		UNIT: mm/in	DWG NO.: X-X25061HI-04A00-PTSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0