


SECTION A-A



SPECIFICATIONS

Material:

Insulator: Glass filled PBT (UL94V-0), Black

Contacts: Brass

Plating: Gold Flash

Electrical Characteristics:

Contact Resistance: 20mΩ Max.

Insulator Resistance: 1000MΩ Min.

Withstanding Voltage: AC 500V

Current Rating: 1.5 AMP

Operating Temperature: -40°C to +105°C



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 闭口短路帽
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW01-TX02-200B
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO: HYC-1709061400
			SHEET NO. 1 OF 1