







SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20M Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Copper Alloy
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
XY-PZ2.54V-02-01P	2*1	0.00	2.54
XY-PZ2.54V-02-02P	2*2	2.54	5.08
XY-PZ2.54V-02-03P	2*3	5.08	7.62
XY-PZ2.54V-02-04P	2*4	7.62	10.16
XY-PZ2.54V-02-05P	2*5	10.16	12.70
XY-PZ2.54V-02-06P	2*6	12.70	15.24
XY-PZ2.54V-02-07P	2*7	15.24	17.78
XY-PZ2.54V-02-08P	2*8	17.78	20.32
XY-PZ2.54V-02-09P	2*9	20.32	22.86
.....			
XY-PZ2.54V-02-40P	2*40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.35	X.*± 5°	APR. Alex	TITLE: 2.54PH H2.5 2xNPIn 180 μ PC3.0 PA6.0 PB2.5 L11.5 6T			
.XX±0.25	.X*± 1	CHK. Jack	DWG NO. XY-PZ2.54V-02-NP			
.XXX±0.2	.XX*± 0.5	DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A