



规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
2. 端子保持力: Terminal Retention
1.0kgf(MIN)

原材料: Material:

1. 塑胶: Housing:
High Temperature Thermoplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC

电镀: Finish:

1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
端子四周镀 30-50U”(MIN) 镍, 镀金区域镀金 1U”
2. 外壳: Shell:
铁-铜壳四周镀镍 50-80U”
Nickel Plating

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-TYPE-A-MWT4P	版本 REV.	A
			X.±0.20	X.*±5°	审核 CHECK	EVA		品名 TITLE	AF 沉板卷边贴板(φ1.2柱)母座	页次 SHEET	1/1
			.X±0.10	.X*±2°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.02	.XX*±1°	单位 UNITS	MM	比例 SCALE	1:1			