





REV.	DESCRIPTION	ECN NO.	NAME	DATE



SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
B254YD-ZS01P-PC032	1	0.00	2.54
B254YD-ZS02P-PC032	2	2.54	5.08
B254YD-ZS03P-PC032	3	5.08	7.62
B254YD-ZS04P-PC032	4	7.62	10.16
B254YD-ZS05P-PC032	5	10.16	12.70
B254YD-ZS06P-PC032	6	12.70	15.24
B254YD-ZS07P-PC032	7	15.24	17.78
B254YD-ZS08P-PC032	8	17.78	20.32
B254YD-ZS09P-PC032	9	20.32	22.86
.....
B254YD-ZS40P-PC032	40	(PIN-1)X2.54	(PIN)X2.54



GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM. TOL.	TITLE: 2.54FH H8.5 2xnPin 90度 Y型 PC3.2 PB12.7 6T			
x. ±0.30	DWG. NO.: B254YD-ZSXP-PC032		CHECKED: MAX	
x.x ±0.20	PART NO.: B254YD-ZSXP-PC032		DRAWN: ELLA	
x.xx ±0.10	UNIT: mm		SCALE: none	SHEET: 1 of 1
GENERAL ANGLE:	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	
X.° ±5°				
X.X° ±1°				
X.XX° ±0.5°				

BXCONN[®]