



REV.	DESCRIPTION	ECN NO.	NAME	DATE

NOTE:
 Technical data:
 Insulator body:PBT+15% G.F UL94-V0
 Current Rating:3 AMP
 Insulator resistance:1000 Megohms min
 Dielectric withstanding:AC/DC 500V.
 Contact Resistance:25mΩ
 Contact material:Bronze.
 plating:Gold or tin over nickel
 Operating Temperature:-40°C to +105°C

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				 
DIM.	TOL.	TITLE: MJ PH2.0 H:3.5				
x.x	±0.25	DWG. NO.: A200D-PT060-B		CHECKED: MAX		
x.xx	±0.20	PART NO.: A200D-PT060-B		DRAWN: ELLA		
x.xxx	±0.10	UNIT: mm		SCALE: none	SHEET: 1 of 1	
GENERAL ANGLE: ±1°		DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL		