




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		D1	REVISED PER ECR-07-029275	10DEC07	HMR	GJ

- 1 SPECIFICATIONS:
MAGNET WIRE #12 - #23 AWG,
.081"(2.06mm)–.022"(0.56mm) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
- 2 POCKET RECOMMENDATION: #1601438
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13210 FIGURE 4.
- 4 TERMINALS SUPPLIED ON REELS,
CAN BE SUPPLIED LOOSE PIECE.



-	-	-
-	-	-
-	-	-
-	-	-
UNPLATED	151-006-000	2-1601138-1
UNPLATED	151-005-000	1601138-1
FINISH	REFERENCE PART NUMBER	TE PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: INCHES	DWN J.WELLER 11JAN2002	Tyco Electronics Corporation Harrisburg, PA 17105-3608
	CHK M.FEHER 11JAN2002	
	APVD K.RANDOLPH 11JAN2002	
	PRODUCT SPEC 108-2239	
MATERIAL BRASS, SPRING HARD	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01[0.25] 3 PLC ± .005[0.13] 4 PLC ± - ANGLES ± 2°	NAME MEDIUM RANGE WIRE TO .130 X .032 TAB SIAMEZE TERMINAL -
	FINISH SEE TABLE	SIZE A2
CUSTOMER DRAWING		SCALE 4:1
WEIGHT -		SHEET 1 OF 1
RESTRICTED TO -		REV D1