



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.09.12	阿树



Technical Data
Material Contact Material: Brass/Phosphor Bronze
Contact plating: Nicker/Gold Flash
Standard: PBT+30%G F
Electrical
Current rating: 3.0Amps/contact ma
Insulator Material: Black Polyester UL94V-0
Withstanding Voltage: 1000V AC/minute Mechanical
Operaing temperature: -40 C° to+105 C°



X2540-A 0 NI B

HOUSING COLOR:
B:BLACK BL:BLUE
Y:YELLOW W:WHITE
GR:GREEN R:RED
CONTACT PLATING:
GF:FULL GOLD FLASH
NI:NICKEL
GN:GOLD+NICKEL

HEIGHT:
0:6mm
1:6.5mm

HOUSING TYPE:
A:OPEN
B:CLOSE
C:LONG

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.54 CONN
CHECKED		UNIT: mm/in	PART NO.: X2540-A0NIB
APPROVED		SIZE: A4	DWG NO.: X-X2540-A0NIB
SCALE			PAGE
N/A			1/1
REVISION			A1