











Specifications

A. Material
Plastic cement: LCP, Black
Contact: Copper Alloy, T=0.20mm
Shell: Copper Alloy, T=0.40mm

B. Plating
Contact Area: 1u" Au over 50u' min. Nickel
Solder Tails: 100u" min. Matte Tin over 50u' min. Nickel
Shell: 60u" min. Nickel

C. Electrical
Current Rating: 1.0A/contact terminal
Voltage Rating: 30V
Power Rating: 30W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.


D. Mechanical & Environmental
Operating Temperature: −25℃ to +85℃
Insertion force: 30.0 N Max
Withdrawal force: 7.0 N Min
Contact retention: 5.0N Min
Durability: 5000 cycles

Pin Numbe	Signal Name
1	VBUS
2	D−
3	D+
4	ID
5	GND


Part Number			Product Description				
PMBFB-R13D-007			Mini USB Receptacle, Type B, Wire Solder, 5 Pin				
DWG.No.	P-MBF-046		Tolerances Unspecified				Units: Metric(mm)
Revision	A0		X.X	±0.35	X°	±5°	
Designed	Lee	09/30/22	X.XX	±0.25	X.X°	±2°	
Approved	Allen	09/30/22	X.XXX	±0.15			

ROHS COMPLIANT 2011/65/EU
Deca-BDEv


Connecting the Future
www.szywf.com.cn
www.szywf.cn




① PE bag




② 1000pcs/bag,and seal it with a sealing machine.




③ 10 bag/case (10K pcs).



④ 10 bag per box, if the last box is added with filler in the space.



⑤ The outer box is sealed with transparent adhesive tape in the shape of "H".



⑥ Paste the product or ROHS label as shown.

Part Number			Product Description					
PMBFB-R13D-007			Mini USB Receptacle, Type B, Wire Solder, 5 Pin					
DWG.No.	P-MBF-046 (2B-5D-8)		Tolerances Unspecified				Units: Metric(mm)	ROHS COMPLIANT 2011/65/EU Deca-BDEv
Revision	A0		X.X	±0.35	X°	±5°		
Designed	Lee	09/30/22	X.XX	±0.25	X.X°	±2°		
Approved	Allen	09/30/22	X.XXX	±0.15				

Connecting the Future
www.szywf.com.cn
www.szywf.cn
Sheet No. 2/2