



**XunPu** 东莞市讯普电子科技有限

Dongguan Xunpu Electronic Technology Co.,

# 承 认 书

## SPECIFICATION FOR APPROVAL

客户名称 Customer: \_\_\_\_\_

贵司料号CUSTOMER P/N: \_\_\_\_\_

FFC cable 0.5mm,16P,total length 100mm,reverse,gold finger 4mm,reinforcing plate 8mm

敝司料号INTERIOR P/N: FFC-0.5-16-100-B-4-8

### 贵公司承认印 Approval signatures




料号/Part No.	签章/Signatures

Send us a copy of reference, thank you!

日期 Date:

拟制/Drawn	陈军
审核/Check	陈军
批准/Approved	陈军





**Precautions**

1. The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

Structure				
NO.	Project	Specification		Remark
1	Insulating film	Print 20624	43um	60V 80C
		Blank film	43um	
2	Stiffeners	Blue	225um	PET
3	Conductor tinning	Thickness	0.035	±0.005
		Width	0.3	±0.03
4	Conductor plating	Electroplate	Tin Sn	≥40u"
		Electroplate		

Size				
Number of conductor cores	N	16		
Spacing	P	0.5	±0.05	
Total spacing	Pt	7.5	±0.08	
Overall width	W	8.5	±0.08	
Edge width	M	0.5	±0.08	
Overall length	L	100	±1.5	
Mating thickness	T1	0.3	±0.05	
Thickness of the thread	T2	0.12	±0.03	
The inclination of the line mouth	A		≤0.3	
Punching inclination	B		≤0.5	
The length of the bare copper at the wire port	S1/S2	4/4	±0.05	
Length of stiffener	B1/B2	8/8	±1	

Ancillary checklists				
NO.	Project	Specification	Quantity	
1				
2				
3				

1. Shelf life: 12 months for gold plating; Tin plating for 6 months.
2. Storage environment: temperature 0°C~38°C; Humidity 20%~70%RH.

Specifications and models:		FFC-0.5-16-100-B-4-8	
Customer part number:		Customer model:	
Version	Content of change	date	
A/O	New production	2022/09/05	



东莞市讯普电子科技有限公司

Name:	FFC flexible cable	Figure number:	XP2024080501	Drawing:	Li ming
Proportion:	FIT	Unit:	Millimetre(mm)	Audit:	Chen Jun
Vision:		Page number:	Page 1 of 1	Approved:	Xiang Yu