



东莞市讯普电子科技有限公司

Dongguan Xunpu Electronic Technology Co., Ltd

承 认 书

SPECIFICATION FOR APPROVAL

客户名称 Customer: _____

贵司料号 CUSTOMER P/N: _____

FFC cable 1.0mm 21P, total length 100mm, co-directional, gold finger 4mm, reinforcing plate 8mm

敝司料号 INTERIOR P/N: _____

FFC-1.0-21-100-A-4-8

贵公司承认印 Approval signatures


料号/Part No.	签章/Signatures

Send us a copy of reference, thank you!

日期 Date:

拟制/Drawn	李明
审核/Check	李军
批准/Approved	向钰





Structure				
NO	Project	Specification	Remark	
1	Insulating film	Print 20624	43um	60V 80C
		Blank film	43um	
2	Stiffeners	Blue	225um	PET
3	Conductor tinning	Thickness	0.035	±0.005
		Width	0.3	±0.03
4	Conductor plating	Electroplate	Tin Sn	≥40u"
		Electroplate		

Size			
Number of conductor	N	21	
Spacing	P	1.0	±0.05
Total spacing	Pt	20	±0.08
Overall width	W	22	±0.08
Edge width	M	1.0	±0.08
Overall length	L	100	±1.5
Mating thickness	T1	0.3	±0.05
Thickness of the	T2	0.12	±0.03
The inclination of the	A	—	≤0.3
Punching inclination	B	—	≤0.5
The length of the bare	S1/S2	4/4	±0.05
Length of stiffener	B1/B2	8/8	±1.5


Ancillary checklists			
NO	Project	Specification	Quantity
1			
2			
3			


Precautions

- The body image is for relationship comparison only, and everything is subject to the specifications of the data sheet.

- Shelf life: 12 months for gold plating; Tin plating for 6
- Storage environment: temperature 0°C-38°C; Humidity

Specifications and models:	FFC-10-21-100-A-4-8		
Customer part number:	Customer model:		
Version	What's Changed	date	
A/O	New production	2022/09/05	

 **XunPu** 东莞市讯普电子科技有限公司

Name:	FFC flexible	Figure number:	XP2022090501	Drawing:	Li ming
Proportion:	1:1	Unit:	Millimetre(mm)	Audit:	Chen Jun
Vision:		Page number:	Page 1 of 1	Approved:	Xiang Yu